

ANKERSMID Condensate vessel ACV 0x0 Series

Application

The liquid collection vessel **ACV 0X0** is specially designed for applications where automatic condensate removal is difficult. When using a peristaltic pump for automatic condensate removal,

When using a peristaltic pump for automatic condensate removal, a sudden surge of liquid can be hard to handle. In these cases the condensate collection vessel can be used as a reservoir or buffer vessel.

For safe operation, the overflow GL25/12 of the condensate vessel ACV 010 can be equipped with a liquid-level sensor and alarm.

* Pictures may vary

Description

The Ankersmid liquid collection vessel ACV 010 is made of industrial quality glass. This ensures high corrosion resistance and the ability to see inside the vessel. A GL25-12 mm clamp connector is provided as condensate inlet.

The outlet valve is a PTFE stopcock, ensuring easy access and hermetic sealing. All contacting parts are made out of glass and PTFE.

A wall-mounting plate is supplied as part of standard delivery. The liquid Alarm Sensor is optional; the electronic of the sensor sends an alarm to the control room or opens a valve (optional) to drain the liquid out.

See more about our liquid sensors ALS on chapter 3-8.

-Vessel with other liquid capacities or materials on request -

- Very corrosion resistant
- Liquid level always visible
- Different tube connections possible
- Level alarm possible
- With integrated outlet cock



ANKERSMID Condensate vessel

Technical data

ACV 0x0 Series

Condensate vessel	ACV 010	ACV 020	ACV 030
Material	Glass	PVC	PVDF
Operating temperature	0 to +80°C	0 to +50°C	0 to +120°C
Storage temperature	-15°C to +65°C		
Operation pressure, max.	2bar	0,5bar	10bar
Capacity	+/- 1Ltr		
Over all dimensions (wxhxd)	160 x 310 x 180	160 x 310 x 135	160 x 310 x 135
Connections	1x GL25-12 Manual valve	3x G1/4"f 2x G1/2"f	2x G1/4"f 1x G1/2"f
Overflow	1x GL25-12	-	-
Weight, approx.	+/- 1kg	+/- 0,5kg	+/- 0,5kg